



UNIVERSAL ROBOTS

A Teradyne Robotics Company

SP7 Smart Panel

Generation 7 · g-Series 01

Technical datasheet

Updated September 2026

Copyright © 2026 by Universal Robots A/S. All rights reserved.



SP7 Smart Panel

General specification

Interface	Optional accessory. Mates with SP7 Smart Panel interface on g-Series tool flange.
Connector type	Pogo-pin. Spring on tool, capture pads on keypad.
Buttons	3x programmable buttons and 1x safety-rated Freedrive / hand-guided control (2PE)
Indicators	2x LED, neutral white
Power supply voltage	5 Vdc
Freedrive	ISO 10218-1:2025
Features	Detachable panel, Smart Skills mapping, Freedrive at the end of the arm

Environment

Operating temperature	0-50 °C
Humidity	≤ 90% RH (non-condensing)
Pollution degree	2

Protection

IP classification	IP65
-------------------	------

Physical

Weight	30 g
--------	------

Compatibility

Robot arm	g-Series
-----------	----------

Contact

UR HQ address

UR HQ phone

UR email

UR website

Universal Robots A/S

Energivej 51

5260 Odense, Denmark

+45 89 93 89 89

sales@universal-robots.com

universal-robots.com